

**NABAKEM®**  
Chemicals & Aerosol



SR-800E

NABAKEM SR-800E (Aluminum Acid  
Cleaner)

**Packaging** Liquid 20kg/PVC Bottle

**Unit :**

## Uses

---

- Removal of oil, grease, rust and scale on the surface of aluminum tank and reactors
- Cleaning of the surfaces made of aluminum and its alloy of vessels and airplanes
- Food container and storage tank made of aluminum and its alloy
- Cleaning of equipment and structure made of aluminum and its alloy

## How to Use

---

- Dilute the product with water under instruction of qualified technician
- Dilution in water
  1. Wipe system : water(100) : undiluted solution(20 ~ 30)(normal temperature)
  2. Spray system : water (100) : undiluted solution (2 ~ 10)(normal temperature)
- Clean by using wiper or brush. Or use spray gun to inject at high pressure for cleaning.
- Wear protective equipment like rubber gloves, boots, protective clothing and safety goggles.
- When using brush or wiper, clean top-down for safety.
- High pressure water rinsing(15kg/cm<sup>2</sup>) is required after use.
- After neutralized cleaning is finished, remove moisture by using compression air or thermal wind.

## Cautions

---

- Wear protective equipment.
- Flush contaminated skin immediately with water.
- Clean top-down for safety.
- High-pressure water rinsing is required for removing residues after use.